# CROSS NEEDLE TYPE SWR&POWER METER SX20/SX40

## OPERATION INSTRUCTION

#### GENERAL

SX20/SX40 CROSS NEEDLE SWR&POWER METER WITH A COUPLE OF METERS INDICATING FORWARD AND REFLECTED

POWER RESPECTIVELY. IT PROVIDES THE DIRECT READ OUT OF THE SWR AND OUTPUT POWER VALUE FROM THE CROSSING OF TWO POINTERS. SETUP

CONNECT THE OUTPUT OF TRANSCEIVER TO THE "TX" CONNECTOR AND ANTENNA TO THE "ANT" CONNECTOR BOTH LOCATED ON THE REAR PANEL OF THE UNIT.

## **OPERATION**

SELECT THE PROPER RANGE LO/HIGT ACCORDING TO YOUR TRANSCEIVER OUTPUT POWER USUALLY SELECT THE "HIGH" RANG FIRST IS STRONGLY SUGGEST.

\* FORWARD POWER

FOLLOW THE FORWARD SCALE AND READ IT OUT.

\*REFLECTED POWER

FOLLOW THE REFLECTED SCALE NAD READ IT OUT.

\*STANDING WAVE RATIO(SWR)
FOLLOW THE SWR CORRESPONDING SCALE FROM THE POINT OF POINTER CROSSING READ IT OUT
REFER TO FIG.1

### CAUTION

\*NO MECHANICAL SHOCK TO BE GIVEN THE UNIT AS IT EMPLOYS PRECISION METERS

\*DO NOT TRANSMIT WITH AN ANTENNA OUT OF TUNED OR OPEN CONDITION AS IT MAY BURN OUT THE METER BY HIGH VOLTAGE .

#### SPECIFICATION

FREQUENCY RANGY: 1.8~200 MHZ SX20; 140~525 MHZ SX40

INPUT IMPEDANCE:50 ohms

POWER RANGE :30W OR 300W SX20 ;15W~150W SX40 SWITCHABLE

POWER ACCURACY:10% AT FULL SCALE
MINI INPUT POWER:2W Sx20; 1W SX40
CONNECTOR: UHF (M TYPE)
DIMENSION: 85Wx87Hx95D
WEIGHT: 290g SX20; 280g SX40

WEIGHT : 290g SX20 NPU FPOWER : DC12V

IN CASE OF 220MHZ BAND MEASUREMENT BOTH FORWARD AND REFLECT POWER TO BE CONVERTED WITH THE FOLLOWING FORMULA .

DIRECT READ OUT IN THE SCALEXO.7=ACTUAL POWER

EX. WHEN DIRECT READ OUT SHOWS 10W, IT SHOULD BE 10Wx0.7=7W

SWR= 
$$\frac{\sqrt{Pf} + \sqrt{Pf}}{\sqrt{Pf} - \sqrt{Pf}}$$
 Pf= FORWARD POWER Pr= REFLECTED POWER

## ACCESSORY: DC POWER INPUT CABLE ONE PIECE

